


ABEL CM


From the reciprocating positive
displacement pump specialist



Compact Diaphragm Pumps

Piston Diaphragm pumps for difficult media

ABEL CM - Performance range: up to 215 m³/h (950 GPM); up to 6.4 MPa (930 psi)



ABEL CM piston diaphragm pumps for raw sewage transfer in a large WWTP in Asia


ABEL CM piston diaphragm (membrane) pumps are single or double-action specialized pumps that are used for difficult media. They are highly resistant to wear, even when used at high pressures over an extended period of time. Their true double-diaphragm technology offers a high degree of safety.

When used as a pump for feeding filter presses, the rugged, automatic flow rate control (which does not use complex electronics) is another impressive feature that makes it even more reliable.

ABEL CM pumps – specialists for difficult media

- For sludge transfer
- Feeding filter presses, rotary kilns, or spray dryers (spray dryer feed pump)
- Raw sewage transfer
- Transfer of abrasive, corrosive, acidic, alkaline, pigmented, viscous, and grainy media

 Available with ATEX certification.



ABEL CM in plastic design for transfer of aggressive fluids

Operational reliability through double diaphragm technology

In the event the product or hydraulic medium penetrates into the intermediate space of the double diaphragm, it is immediately detected by the integrated control function before the product gets into the hydraulic media or vice versa. Alternatively, an automatic alarm is activated by an electrical control.

The advantages of ABEL CM

- Operational reliability through double diaphragm technology
- Up to 215 m³/h (950 GPM)
- Up to 6.4 MPa (930 psi)
- Tested design
- Optimal controllability
- Long life
- Serviceability
- Plastic design (Polypropylene wet end) available

ABEL piston diaphragm pumps have built our reputation as a leading manufacturer of reciprocating positive displacement pumps, establishing ABEL as the world market leader in filter press feeding (Hydraulic Institute, 1999).

The CM technology

- Optimal design to withstand high pressures
- Maximum filling efficiency
- Hermetically sealed
- Product side without gland packings
- Ball or conical valves
- Valve housing with inspection openings
- Visual or electrical diaphragm control indicator
- Safety valve and automatic liquid supplement in the primary circulation
- Central pressure control during filter press operation
- Automatic diaphragm position control

Optimum design

The technical details described below that make the ABEL compact diaphragm pumps so unparalleled in function and quality.



Ball valves with inspection opening and diaphragm leakage detection device



Tested, stable design. ABEL CM piston diaphragm pump for filter press feed



CM piston diaphragm pumps in a water treatment works in Northern Ireland

Controlled flow characteristics for feeding filter presses

The diaphragm stroke control by means of the control valve automatically adapts the flow rate to the throughput characteristics of the filter presses.

The control valve is calibrated for each application on the ABEL test stand so as to limit the final operating pressure.

Another plus for operational reliability

In many situations where the environment is not conducive to using electronic speed controls, especially in the surface refinement sector and the disposal industry, customers avoid using frequency converters for the control of filter press feed pumps. In these situations, the ABEL CM piston diaphragm pump proves its strength.

Valve balls for precision and durability

Through the combination of two soft materials ABEL Compact Diaphragm Pumps run smoothly.


In the standard version the pumps are fitted with machine-ground polyurethane valve balls of highest precision and seats made of polyethylene or polyurethane.

Of course, many other combinations are available.

By utilizing a pressure dependent diaphragm stroke control system, the capacity of the pump is automatically reduced as the system pressure increases without the use of a frequency converter.

Valve for diaphragm stroke control

double diaphragm



Industries and applications



ABEL CM-pump for spray dryer feed

Use of Compact Diaphragm Pumps as Feed Pumps for Spray Dryers

ABEL CM piston diaphragm pumps feed ceramic slip with defined pressure through the spray nozzles into the drying chamber of the spray dryer.

The use of existing vertical plunger pumps caused the following problems:

- Leakage in the cylinder due to highly erosive slurry
- Damage of the piston caused by grain content in the slip
- High water consumption due to packing gland flushing
- Difficult replacement of spare parts due to complicated design of the pumps
- Difficult and messy maintenance due to the use of oil as hydraulic medium
- Pulsation in the discharge pipe

ABEL CM piston diaphragm pumps enable the transfer of highly abrasive, even grainy suspensions by using high-strength special diaphragm and ball valves, which prevent the medium being pumped from coming into contact with the piston and other mechanical control elements of the pump.

The use of big-volume pulsation dampeners dependably avoids high pulsation and therefore the discontinuous discharge of the slurry over the entire pressure range. A frequency controlled drive allows exact flow adjustment in dependence upon the nozzle wear rate and thus a pressure control and an adaption to the handling of various slip qualities to different granulates.



Waste water – sewage treatment works and pumping stations



Energy/power plants – flue gas desulphurization



Cement industry – rotary kiln feed



Steel works – transfer of pickle and scaling slurries



Diaphragm Pumps
Solids Handling Pumps
High Pressure Pumps
Marine Pumps

For North America

ABEL Pumps, L.P.
600 N. Bell Ave, Bldg. 2, Suite 250
Carnegie, PA 15106, USA
Phone +1 (412) 741 3222
Fax +1 (412) 741 2599
mail@abelpumps.com

For Spain, Portugal, Central and South America

ABEL Equipos S.A.
C/Anochecer 2, Edificio el Torreón
28223 Pozuelo de Alarcón, Spain
Phone +34 (91) 715 4848
Fax +34 (91) 348 3665
mail@abelequipos.es

ABEL GmbH
Abel-Twiete 1
D - 21514 Büchen, Germany

Phone +49 (4155) 818-0
Fax +49 (4155) 818-499
mail@abel.de • www.abel.de